

Specification Sheet

Part Number: 151-01240



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

Bundling Clip with Oval Fir Tree, 1.52" L, 0.02 - 0.24" Panel Thickness, PA66HIRHS, Natural, 10,000/ctn

Article Number	151-01240
Type	BCFTOVAL2
Color	Natural (NA)
Quantity Per	pack
Product Description	HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.
Short Description	Bundling Clip with Oval Fir Tree, 1.52" L, 0.02 - 0.24" Panel Thickness, PA66HIRHS, Natural, 10,000/ctn
Global Part Name	BCFTOVAL2-PA66HIRHS-NA

Length L (Imperial)	1.52
Length L (Metric)	38.7
Fixation Method	Fir Tree for oval holes
Height H (Imperial)	0.60
Height H (Metric)	15.45
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.25 x 0.50 " 0.24 x 0.48 " 0.27 x 0.47 "
Mounting Hole Diameter D (Metric)	7.0 x 12.0 mm 6.2 x 12.2 mm 6.5 x 13.0 mm 6.5 x 12.5 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.50
Mounting Hole Diameter D Max (Metric)	13.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut	PA66HIRHS
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	10000
Package Quantity (Metric)	10000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)