

Specification Sheet

Part Number: 151-01296

HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications.

Detailed designs include anti-rattle disc features, anti-rotation oval fir trees, and clamps for mounting on edges.



HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers.

Connector Clip with Oval Fir Tree, 9.0 - 17.0mm Hole Dia, PA66HIRHSUV, Black, 3000/carton

Article Number	151-01296
Type	CC18
Color	Black (BK)
Quantity Per	pack
Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description	Connector Clip with Oval Fir Tree, 9.0 - 17.0mm Hole Dia, PA66HIRHSUV, Black, 3000/carton
Global Part Name	CC18-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	35
Minimum Tensile Strength (Metric)	155
Length L (Imperial)	1.19
Length L (Metric)	30.29
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.80
Width W (Metric)	20.32
Height H (Imperial)	0.93
Height H (Metric)	23.57
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.37
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	9.5
Mounting Hole Diameter D (Imperial)	0.35 x 0.67 "

Mounting Hole Diameter D (Metric)	9.0 x 17.0 mm
-----------------------------------	---------------

Mounting Hole Diameter D Min (Imperial)	0.35
---	------

Mounting Hole Diameter D Max (Imperial)	0.35
---	------

Mounting Hole Diameter D Max (Metric)	9.0
---------------------------------------	-----

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
----------	--

Material Shortcut	PA66HIRHSUV
-------------------	-------------

UV Resistant (Yes/No)	Yes
-----------------------	-----

Use Conditions	For Indoor and Outdoor Use
----------------	----------------------------

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
-----------------------	-----------------------------------

Reach Compliant (Article 33)	Yes
------------------------------	-----

Package Quantity (Imperial)	3000
-----------------------------	------

Package Quantity (Metric)	3000
---------------------------	------

Customs Number	3926909988
----------------	------------

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)