

## Specification Sheet

Part Number: 151-01297

HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications.

Detailed designs include anti-rattle disc features, anti-rotation oval fir trees, and clamps for mounting on edges.

HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers.



Connector Clip with Oval Fir Tree, 8.0 - 15.0mm Hole Dia, PA66HIRHSUV, Black, 5000/carton

Article Number 151-01297

Type CC16

Color Black (BK)

Quantity Per pack

**Product Description** Connector Clips are designed with various fixing point designs, to accommodate the many connectors out in the market. This specific connector clip is designed for a commonly used automotive connector. The width and the height of the fixation point creates minimal rattle when secured. The innovative design of the fir tree creates an interface with four different size holes that are common in the automotive industry. The fir tree branch design on all four sides makes a 360-degree interface with the panel, creating a more secure fit into the hole.

Short Description	Connector Clip with Oval Fir Tree, 8.0 - 15.0mm Hole Dia, PA66HIRHSUV, Black, 5000/carton
Global Part Name	CC16-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	25
Minimum Tensile Strength (Metric)	110
Length L (Imperial)	1.18
Length L (Metric)	30.0
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.72
Width W (Metric)	18.2
Height H (Imperial)	0.92
Height H (Metric)	23.4
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.31
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	7.75
Mounting Hole Diameter D (Imperial)	0.31 x 0.59 " 0.31 x 0.55 "

Mounting Hole Diameter D (Metric) 8.0 x 15.0 mm 8.0 x 14.0 mm

Mounting Hole Diameter D Min (Imperial) 0.31

Mounting Hole Diameter D Max (Imperial) 0.31

Mounting Hole Diameter D Max (Metric) 8.0

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

UV Resistant (Yes/No) Yes

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 5000

Package Quantity (Metric) 5000

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)