

Specification Sheet

Part Number: 151-01311

Bundling clip allows bundle to be parallel, perpendicular or offset from the panel and mounting hole for routing versatility.

Compact I-beam design provides a robust solution for all bundles, small to large.

Used in conjunction with HellermannTyton's 4x oval push pins, bundling clip prevents rotation of the bundle.

Oval hole can also be used as a portable hole joining two routings together.



Bundling Clip, 90 Deg with 6.5x12.5 Oval Hole, 40mm Long, PA66HIRHSUV, Black, 4000/ctn

Article Number	151-01311
Type	TC90OVAL
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's bundling clips allow a harness to be routed around a corner and attached to the panel at this location.
Short Description	Bundling Clip, 90 Deg with 6.5x12.5 Oval Hole, 40mm Long, PA66HIRHSUV, Black, 4000/ctn
Global Part Name	TC90OVAL-PA66HIRHSUV-BK

Length L (Imperial)	1.47
Length L (Metric)	37.3
Fixation Method	Bolt
Width W (Imperial)	0.59
Width W (Metric)	15.0
Height H (Imperial)	1.66
Height H (Metric)	40.8
Mounting Hole Diameter D (Imperial)	0.27 x 0.51 "
Mounting Hole Diameter D (Metric)	6.5 x 12.5 mm
Mounting Hole Diameter D Min (Imperial)	0.27
Mounting Hole Diameter D Max (Imperial)	0.51
Mounting Hole Diameter D Max (Metric)	12.5
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV

Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)