

Specification Sheet

Part Number: 151-01531



Inserts snap precisely into the body of Ratchet Clamps, making installation easy.

Added level of insulation reduces bundle movement in addition to protecting cables and hoses.

Ratchet Clamp Size B Soft Insert, TPE, Black, 100/bg

Article Number	151-01531
Type	RCINSERTB
Color	Black (BK)
Quantity Per	pack
Product Description	Soft Inserts snap into the body of HellermannTyton's Ratchet Clamps. They provide an added level of protection for sensitive bundles, especially in high-vibration applications.
Short Description	Ratchet Clamp Size B Soft Insert, TPE, Black, 100/bg
Global Part Name	RCINSERTB-TPE-BK

Fixation Method	Others
Variant	Rubber profile
Width W (Imperial)	0.79
Width W (Metric)	20.0
Bundle Diameter Min (Imperial)	0.34
Bundle Diameter Min (Metric)	8.7
Bundle Diameter Max (Imperial)	0.61
Bundle Diameter Max (Metric)	15.5
Material	Thermoplastic Elastomer (TPE)
Material Shortcut	TPE
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor Use Only
Plenum Rating	AH-2
Operating Temperature	-40°F to +194°F (-40°C to +90°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)