

## Specification Sheet

Part Number: 151-01566

Two-piece ratcheting wedge design allows for easy, positive-locking size adjustment.

Peel and stick 3M™ VHB™ adhesive inside clip increases grip and enables one-hand installation.

Heat-stabilized, glass-filled PA66 assembly delivers remarkable extraction force without drilling.

Three sizes cover a wide range of mounting thicknesses, reducing part inventory.



4-way, wide slot accommodates our heavy-duty and Wide-Strap Series Cable Ties.

Wedge Clip, 0.16 - 0.35" Panel Thickness, PA66HSGF, Black, 200/bag

Article Number 151-01566

Type BCBLGA

Color Black (BK)

Quantity Per pack

## Product Description

The Wedge Clip, paired with any HellermannTyton heavy duty Cable Tie, routes cables along a frame or rail in vertical or horizontal applications. A robust design and durable materials make it ideal for extreme-duty applications. The integrated wedge mechanism slides along a stepped grade until snug against the mounting surface. Inside the clip is a 3M™ VHB™ (Very High Bond) adhesive pad, which actually builds strength over time. This holds the clip to the work surface instantly, enabling installers to place it into position without worrying about it falling off prior to fastening. The combination of adhesive and the clip's vice-like compression result in incredible extraction force without the need to drill holes. The Wedge Clip is offered in three sizes.

## Short Description

Wedge Clip, 0.16 - 0.35" Panel Thickness, PA66HSGF, Black, 200/bag

## Global Part Name

BCBLGA-PA66HSGF30-BK

Length L (Imperial)

1.21

Length L (Metric)

30.8

Fixation Method

Edge Clip

Width W (Imperial)

1.13

Width W (Metric)

28.6

Height H (Imperial)

1.70

Height H (Metric)

43.10

Cable Tie Width Max (Imperial)

0.59

Cable Tie Width Max (Metric)

15.0

Panel Thickness Min (Imperial)	0.16
Panel Thickness Max (Imperial)	0.35
Panel Thickness Min (Metric)	9.0
Panel Thickness Max (Metric)	9.0
Material	Polyamide 6.6, heat stabilized, glass fiber reinforced (PA66HSGF30%)
Material Shortcut	PA66HSGF30
Adhesive	Acrylic foam
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +284°F (-40°C to +140°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	200

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)