

Specification Sheet

Part Number: 151-01681



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

90 Degree Bundling Clip, with 4x Oval, 50lb Tensile Strength, PA66HIRHSUV, Black, 1000/pkg

Article Number	151-01681
Type	BCFTOVALAPILLAR
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's bundling clips allow a harness to be routed around a corner and attached to the panel at this location.
Short Description	90 Degree Bundling Clip, with 4x Oval, 50lb Tensile Strength, PA66HIRHSUV, Black, 1000/pkg
Global Part Name	BCFTOVALAPILLAR-PA66HIRHSUV-BK

Length L (Metric)	45.7
Offset Length (Metric)	32.0
Fixation Method	Fir Tree for oval holes
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm 6.5 x 12.5 mm 7.0 x 12.0 mm 6.5 x 13.0 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)