

Specification Sheet

Part Number: 151-02051

HellermannTyton's 4x oval fir tree prevents bundle rotation while providing best-in-class installation and extraction resistance for four common oval sizes.

Angled connector clip allows for clearance from obstructions and sheet metal contours.



Connector clip design meets USCAR EWCAP-005-11 clip slot specifications, assuring compliance.

Connector Clip with Oval Fir Tree, 6.2 - 13.0mm Hole Dia, PA66HIRHSUV, Black, 5000/carton

Article Number	151-02051
Type	CC22
Color	Black (BK)
Quantity Per	pack
Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
Short Description	Connector Clip with Oval Fir Tree, 6.2 - 13.0mm Hole Dia, PA66HIRHSUV, Black, 5000/carton

Global Part Name	CC22-PA66HIRHSUV-BK
Length L (Imperial)	1.01
Length L (Metric)	25.71
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.69
Width W (Metric)	17.53
Height H (Metric)	26.0
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.26 x 0.50 " 0.26 x 0.51 " 0.24 x 0.48 " 0.28 x 0.47 "
Mounting Hole Diameter D (Metric)	6.5 x 12.5 mm 6.5 x 13.0 mm 6.2 x 12.2 mm 7.0 x 12.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.24
Mounting Hole Diameter D Max (Metric)	6.2

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)