

Specification Sheet

Part Number: 151-02099



Positions bundles off cross members and frame rails to prevent abrasion and chafing.

Metal insert bushing accommodates high-torque installation.

Made with high-impact, heat stabilized, and UV material ideal for trucking and heavy equipment environments.

High Torque Axial Mount, 0.327" Bolt Hole Dia, PA66HIRHSUV, Black, 500/pkg

Article Number	151-02099
----------------	-----------

Type	SAM320B-R
------	-----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's axial oval mount stands off bundles from frame rails and cross members to prevent them from rubbing and chafing. The axial oval mount accommodates cable ties up to 0.5" wide. The hole on the mount was designed to fit a 5/16" bolt.
---------------------	--

Short Description	High Torque Axial Mount, 0.327" Bolt Hole Dia, PA66HIRHSUV, Black, 500/pkg
-------------------	--

Global Part Name	SAM320B-R-PA66HIRHSUV-BK
------------------	--------------------------

Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	533
Length L (Imperial)	1.18
Length L (Metric)	29.9
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.98
Width W (Metric)	25.0
Height H (Imperial)	1.77
Height H (Metric)	44.9
Cable Tie Width Max (Imperial)	0.5
Cable Tie Width Max (Metric)	12.7
Mounting Hole Diameter D (Imperial)	0.33 "
Mounting Hole Diameter D (Metric)	8.31 mm
Mounting Hole Diameter D Max (Metric)	8.31
Stud Diameter (Metric)	8.0 mm
Stud Diamater (Imperial)	0.31

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Maximum Torque (kgf-cm)	1576.0
Maximum Torque (lbf-ft)	114.0
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)