

## Specification Sheet

Part Number: 151-02206

Non-rotating fir tree provides easy insertion with high extraction resistance for 8x14 mm and 8x15 mm oval holes.

Meets installation and extraction requirements of SAE/USCAR-2, for easy installation with reliable performance.

Short fir tree avoids obstructions on opposite side of panel.

Connector clip design meets USCAR EWCAP-005-11 clip slot specifications, assuring compliance.



Connector Clip with Oval Fir Tree, 8.0 - 15.0mm Hole Dia, PA66HIRHSUV, Black, 5000/carton

|                |           |
|----------------|-----------|
| Article Number | 151-02206 |
|----------------|-----------|

|      |       |
|------|-------|
| Type | CC16R |
|------|-------|

|       |            |
|-------|------------|
| Color | Black (BK) |
|-------|------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                                                                                           |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly. |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                                         |                                                                                           |
|-----------------------------------------|-------------------------------------------------------------------------------------------|
| Short Description                       | Connector Clip with Oval Fir Tree, 8.0 - 15.0mm Hole Dia, PA66HIRHSUV, Black, 5000/carton |
| Global Part Name                        | CC16R-PA66HIRHSUV-BK                                                                      |
| Length L (Imperial)                     | 1.18                                                                                      |
| Length L (Metric)                       | 30.0                                                                                      |
| Fixation Method                         | Fir Tree for oval holes                                                                   |
| Width W (Imperial)                      | 0.72                                                                                      |
| Width W (Metric)                        | 18.2                                                                                      |
| Height H (Imperial)                     | 0.92                                                                                      |
| Height H (Metric)                       | 23.4                                                                                      |
| Panel Thickness Min (Imperial)          | 0.02                                                                                      |
| Panel Thickness Max (Imperial)          | 0.12                                                                                      |
| Panel Thickness Min (Metric)            | 0.6                                                                                       |
| Panel Thickness Max (Metric)            | 3.0                                                                                       |
| Mounting Hole Diameter D (Imperial)     | 0.31 x 0.59 " 0.31 x 0.55 "                                                               |
| Mounting Hole Diameter D (Metric)       | 8.0 x 15.0 mm 8.0 x 14.0 mm                                                               |
| Mounting Hole Diameter D Min (Imperial) | 0.33                                                                                      |

Mounting Hole Diameter D Max (Imperial) 0.33

Mounting Hole Diameter D Max (Metric) 8.0

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

UV Resistant (Yes/No) Yes

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 5000

Package Quantity (Metric) 5000

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)