

Specification Sheet

Part Number: 151-02432



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

Clip can be installed by hand – no need for hardware or tools.

Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 2.4" Long, 0.03 - 0.22" Panel Thickness, PA66HIRHS, Natural, 2500/carton

Article Number	151-02432
----------------	-----------

Type	SOC8FT8
------	---------

Color	Natural (NA)
-------	--------------

Quantity Per	pack
--------------	------

Product Description	Tape clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes.
---------------------	--

Short Description	Standoff Bundling Clip, 2.4" Long, 0.03 - 0.22" Panel Thickness, PA66HIRHS, Natural, 2500/carton
-------------------	--

Global Part Name	SOC8FT8-PA66HIRHS-NA
------------------	----------------------

Length L (Imperial)	2.4
Length L (Metric)	61
Offset Length (Imperial)	0.625
Offset Length (Metric)	15.9
Fixation Method	Fir Tree
Width W (Imperial)	0.47
Width W (Metric)	12.0
Height H (Imperial)	0.88
Height H (Metric)	22.4
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.22
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	5.5
Mounting Hole Diameter D (Imperial)	0.30 - 0.39 "
Mounting Hole Diameter D (Metric)	M10 x 1.5 7.6 - 10.0 mm
Mounting Hole Diameter D Min (Imperial)	0.29

Mounting Hole Diameter D Max (Imperial) 0.32

Mounting Hole Diameter D Max (Metric) 10.0

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut PA66HIRHS

Flammability UL 94 HB

Halogen Free Yes

UV Resistant (Yes/No) No

Use Conditions For Indoor Use Only

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 2500

Package Quantity (Metric) 2500

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)