

Specification Sheet

Part Number: 151-02451



Dual pipe clip secures two routings together while keeping them separated, to prevent chafing or heat transfer

Inverted retaining legs and narrow opening prevent inadvertent disengagement

Controlled flex and angled entry promote easy installation

Tube and Pipe Clip 1x4 and 1x5mm Diameter, PA66HIRHSUV, Black, 10,000/ctn

Article Number	151-02451
Type	PC4X1-5X1
Color	Black (BK)
Quantity Per	pack
Product Description	An ultra-secure routing clip connected to a round or oval fixing for easy insertion into an existing panel hole.
Short Description	Tube and Pipe Clip 1x4 and 1x5mm Diameter, PA66HIRHSUV, Black, 10,000/ctn
Global Part Name	PC4X1-5X1-PA66HIRHSUV-BK

Length L (Imperial)	0.32
Length L (Metric)	8.2
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4.0
Bundle Diameter Max (Imperial)	0.2
Bundle Diameter Max (Metric)	5.0
Height H (Imperial)	0.72
Height H (Metric)	18.2
Depth D (Imperial)	0.39
Depth D (Metric)	10.0
Diameter D (Imperial)	0.185
Diameter D (Metric)	4.7
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	10000
Package Quantity (Metric)	10000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)