

## Specification Sheet

Part Number: 151-02452



4x Pipe Clip secures four routings together while keeping them separated, to prevent chafing or heat transfer

Inverted retaining legs and narrow opening prevent inadvertent disengagement

Controlled flex and angled entry promote easy installation

Tube and Pipe Clip 2x4 and 2x5mm Diameter, PA66HIRHSUV, Black, 10,000/ctn

|                |           |
|----------------|-----------|
| Article Number | 151-02452 |
|----------------|-----------|

|      |           |
|------|-----------|
| Type | PC4X2-5X2 |
|------|-----------|

|       |            |
|-------|------------|
| Color | Black (BK) |
|-------|------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                        |
|---------------------|------------------------------------------------------------------------------------------------------------------------|
| Product Description | This clip features a modular design that can be used individually or lined together to secure multiple pipes or hoses. |
|---------------------|------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                           |
|-------------------|---------------------------------------------------------------------------|
| Short Description | Tube and Pipe Clip 2x4 and 2x5mm Diameter, PA66HIRHSUV, Black, 10,000/ctn |
|-------------------|---------------------------------------------------------------------------|

|                  |                        |
|------------------|------------------------|
| Global Part Name | PC4X2-5X2-PA66HIRHS-BK |
|------------------|------------------------|

|                                |                                                                  |
|--------------------------------|------------------------------------------------------------------|
| Length L (Imperial)            | 0.66                                                             |
| Length L (Metric)              | 16.7                                                             |
| Width W (Imperial)             | 0.39                                                             |
| Width W (Metric)               | 10.0                                                             |
| Bundle Diameter Min (Imperial) | 0.16                                                             |
| Bundle Diameter Min (Metric)   | 4.0                                                              |
| Bundle Diameter Max (Imperial) | 0.2                                                              |
| Bundle Diameter Max (Metric)   | 5.0                                                              |
| Height H (Imperial)            | 0.72                                                             |
| Height H (Metric)              | 18.2                                                             |
| Material                       | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| Material Shortcut              | PA66HIRHS                                                        |
| UV Resistant (Yes/No)          | No                                                               |
| Use Conditions                 | For Indoor and Outdoor Use                                       |
| Operating Temperature          | -40°F to +221°F (-40°C to +105°C)                                |

|                              |            |
|------------------------------|------------|
| Reach Compliant (Article 33) | Yes        |
| ROHS Compliant               | Yes        |
| Package Quantity (Imperial)  | 10000      |
| Package Quantity (Metric)    | 10000      |
| Customs Number               | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)