

Specification Sheet

Part Number: 151-02551

Connector Clip with tape bar secures connectors with USCAR 11 mm slot and provides strain relief for the connector and wiring assembly.

Compact I-beam design provides a robust solution for all bundles, small to large.

Dog bone ends help secure tape or tie, preventing bundling clip from slipping off bundle.

Connector clip design meets USCAR EWCAP-005-11 clip slot specifications, assuring compliance.

Meets installation and extraction requirements of SAE/USCAR-2, for easy insertion and reliable performance.



Article Number	151-02551
----------------	-----------

Type	SOC25SO9CC11
------	--------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	USCAR Connector Clip with I-beam Bundling Clip, 11mm, POM, Black, 5000/ctn
Global Part Name	SOC25SO9CC11-POM-BK
Length L (Imperial)	1.96
Length L (Metric)	50.0
Width W (Imperial)	0.427
Width W (Metric)	10.85
Height H (Imperial)	0.539
Height H (Metric)	13.7
Material	Polyacetal (POM)
Material Shortcut	POM
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes

Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)