

Specification Sheet

Part Number: 151-02552



The 360 degree locking enclosure dynamically fits a range of bundle sizes.

Clamp can be opened for bundle maintenance.

Low-profile release tab won't interfere with bundle or nearby routing.

Non-rotating fir tree demonstrates easy insertion with high extraction resistance.

LOC Locking Clamp, 10-14 mm, with 4 x Oval Fir Tree, PA66HIRHSUV, Black, 1000/ctn

Article Number	151-02552
----------------	-----------

Type	LOC10-14FTOVAL
------	----------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The Locking Clamp is ideal for fastening wire and cable bundles to panels. Its uniquely engineered fir tree holds tightly in pre-stamped hole sizes from 9x12 mm to 9x14 mm. The locking clamp mechanism dynamically fits various bundle sizes, while an integrated cable tie saddle allows installers to add additional cable runs. The clamp is manufactured of an impact-modified Polyamide 6.6 material for increased flexibility, heat resistance and UV stabilization to deliver years of dependable performance. It is easy to install and operate with a single hand and does not require tools, saving time and labor costs.
---------------------	--

Short Description	LOC Locking Clamp, 10-14 mm, with 4 x Oval Fir Tree, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	LOC10-14FTOVAL-PA66HIRHSUV-BK
Length L (Imperial)	1.09
Length L (Metric)	27.6
Fixation Method	Fir Tree
Width W (Imperial)	0.47
Width W (Metric)	12.0
Bundle Diameter Min (Imperial)	0.39
Bundle Diameter Min (Metric)	10.0
Bundle Diameter Max (Imperial)	0.55
Bundle Diameter Max (Metric)	14.0
Height H (Imperial)	1.71
Height H (Metric)	43.5
Depth D (Imperial)	0.47
Depth D (Metric)	12.0
Panel Thickness Min (Imperial)	0.02

Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.26 x 0.51 " 0.26 x 0.49 " 0.24 x 0.48 " 0.28 x 0.47 "
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm 7.0 x 12.0 mm 6.5 x 13.0 mm 6.5 x 12.5 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.51
Mounting Hole Diameter D Max (Metric)	13.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)