

Specification Sheet

Part Number: 151-02567

Easy to install, remove and reposition with just a quarter-turn – no tools necessary.

Multi-directional cable tie slot allows for routing a bundle parallel to or perpendicular to the frame.

Low profile is ideal for cramped spaces.



Designed to fit an 80/20 profile with a T-slot of 8 mm (0.32") and external dimensions of 40 mm (1.5").

Aluminum Frame Mount for 1.5" Frame, 2.5 - 3.0mm Panel Thickness, PA66MP+, Blue, 100/bg

|                     |                                                                                                                                                                                                                                                                                                                                                         |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 151-02567                                                                                                                                                                                                                                                                                                                                               |
| Type                | MCAFLM30-1                                                                                                                                                                                                                                                                                                                                              |
| Color               | Blue (BU)                                                                                                                                                                                                                                                                                                                                               |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                                                                    |
| Product Description | Aluminum frame mounts can be used with 20, 30 or 40 mm square frames from the major aluminum frame manufacturers. As there is no need to screw them in place, these mounts offer maximum ease of use and fast installation. The mounts contain metal particles for detection in processing plants where the potential for contamination is undesirable. |

|                                |                                                                                         |
|--------------------------------|-----------------------------------------------------------------------------------------|
| Short Description              | Aluminum Frame Mount for 1.5" Frame, 2.5 - 3.0mm Panel Thickness, PA66MP+, Blue, 100/bg |
| Global Part Name               | MCAFLM30-1-PA66MD-BU                                                                    |
| Length L (Imperial)            | 1.02                                                                                    |
| Length L (Metric)              | 26.0                                                                                    |
| Fixation Method                | Profile rail                                                                            |
| Width W (Imperial)             | 0.71                                                                                    |
| Width W (Metric)               | 18                                                                                      |
| Cable Ties                     | T18 - T50                                                                               |
| Height H (Imperial)            | 0.68                                                                                    |
| Height H (Metric)              | 17.2                                                                                    |
| Panel Thickness Min (Imperial) | 0.10                                                                                    |
| Panel Thickness Max (Imperial) | 0.12                                                                                    |
| Panel Thickness Min (Metric)   | 2.5                                                                                     |
| Panel Thickness Max (Metric)   | 3.0                                                                                     |

|                              |                                          |
|------------------------------|------------------------------------------|
| Material                     | Polyamide 6.6, metal detectable (PA66MD) |
| Material Shortcut            | PA66MD                                   |
| UV Resistant (Yes/No)        | No                                       |
| Use Conditions               | For Indoor Use Only                      |
| Operating Temperature        | -40°F to +185°F (-40°C to +85°C)         |
| Reach Compliant (Article 33) | No                                       |
| ROHS Compliant               | Yes                                      |
| Package Quantity (Imperial)  | 100                                      |
| Package Quantity (Metric)    | 100                                      |
| Customs Number               | 3926909988                               |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)