

Specification Sheet

Part Number: 151-02737

One-piece ratchet closure allows for easy installation during pre- or final assembly.

Easy release feature simplifies quick adjustments and maintenance.

Low fire hazard PA666V0 material is designed specifically for rail applications.

Stainless steel mounting plate tolerates high torque and provides superior corrosion resistance against chemicals, salt spray and contact with dissimilar metals.

Straight, 180° mounting plate is ideal for applications requiring a flush mount set off from the mounting hole.



Ratchet P-Clamp, 0.76 - 1.42" Bundle Dia, 180° Short, 0.33" Hole Dia, PA666V0/SS304, Black, 160/ctn

Article Number 151-02737

Type RCC180SM8SS

Color Black (BK)

Quantity Per pack

Product Description

The Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables simply by using a flat-head screwdriver. This nondestructive release allows the clamp to be reused without removing or replacing any bolts or screws. Low fire hazard material is designed specifically for rail applications.

Short Description

Ratchet P-Clamp, 0.76 - 1.42" Bundle Dia, 180° Short, 0.33" Hole Dia, PA666V0/SS304, Black, 160/ctn

Global Part Name

RCC180SM8SS-PA666V0/SS304-BK

Minimum Tensile Strength (Imperial) 100

Minimum Tensile Strength (Metric) 445

Length L (Imperial) 6.15

Length L (Metric) 156.1

Fixation Method Screw Mounting

Variant Short

Width W (Imperial) 1.37

Width W (Metric) 34.9

Bundle Diameter Min (Imperial) 0.76

Bundle Diameter Min (Metric) 19.4

Bundle Diameter Max (Imperial)	1.42
Bundle Diameter Max (Metric)	36.0
Mounting Hole Diameter D (Imperial)	0.33 "
Mounting Hole Diameter D (Metric)	8.4 mm
Stud Diameter (Metric)	M8
Mounting Hole Centers (Imperial)	2.45
Material	Stainless Steel (SS304) Polyamide 6.6/6, V0 (PA666V0)
Material Shortcut	SS304 PA666V0
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Certification/Specification

EN [45545-2] ASTM 1354 ASTM E 162 ASTM E 662

Package Quantity (Imperial) 160

Package Quantity (Metric) 160

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)