

## Specification Sheet

Part Number: 151-02980



Can be easily assembled to convoluted tubing and reliably remain in position

Internal rib prevents movement or rattling

Multiple bracket configurations mount to a variety of surfaces

Releasable to allow for maintenance

Conduit Clamps, Size 13, Mounting Hole 6.5 mm, Offset 40.5 mm, PA66, Black, 50/pkg

|                |           |
|----------------|-----------|
| Article Number | 151-02980 |
|----------------|-----------|

|      |              |
|------|--------------|
| Type | CDC13S40.5M6 |
|------|--------------|

|       |            |
|-------|------------|
| Color | Black (BK) |
|-------|------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                              |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | The Convoluted Tubing Clamp provides a quick method for securing and routing convoluted tubing. The clamp has an internal rib that prevents movement of the tubing and rattling. Living hinge allows placement and positioning of tubing before locking in place. Convoluted tubing clamps are available in various tubing diameters. Choose from arrowhead, fir tree, bundling clip, bracket and dual clamp configurations. |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                                    |
|-------------------|------------------------------------------------------------------------------------|
| Short Description | Conduit Clamps, Size 13, Mounting Hole 6.5 mm, Offset 40.5 mm, PA66, Black, 50/pkg |
|-------------------|------------------------------------------------------------------------------------|

|                  |                      |
|------------------|----------------------|
| Global Part Name | CDC13S40.5M6-PA66-BK |
|------------------|----------------------|

|                     |      |
|---------------------|------|
| Length L (Imperial) | 2.59 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Length L (Metric) | 65.7 |
|-------------------|------|

|         |        |
|---------|--------|
| Variant | Clamps |
|---------|--------|

|                    |     |
|--------------------|-----|
| Width W (Imperial) | 0.9 |
|--------------------|-----|

|                  |    |
|------------------|----|
| Width W (Metric) | 23 |
|------------------|----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Max (Imperial) | 0.51 |
|--------------------------------|------|

|                              |      |
|------------------------------|------|
| Bundle Diameter Max (Metric) | 13.0 |
|------------------------------|------|

|                     |      |
|---------------------|------|
| Height H (Imperial) | 2.07 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Height H (Metric) | 52.8 |
|-------------------|------|

|                             |      |
|-----------------------------|------|
| Inner Diameter D (Imperial) | 0.69 |
|-----------------------------|------|

|                           |      |
|---------------------------|------|
| Inner Diameter D (Metric) | 17.6 |
|---------------------------|------|

|                       |      |
|-----------------------|------|
| Diameter D (Imperial) | 0.55 |
|-----------------------|------|

|                     |      |
|---------------------|------|
| Diameter D (Metric) | 14.0 |
|---------------------|------|

|                             |     |
|-----------------------------|-----|
| Nominal Diameter (Imperial) | 0.5 |
|-----------------------------|-----|

|                           |      |
|---------------------------|------|
| Nominal Diameter (Metric) | 13.0 |
|---------------------------|------|

|                                     |                                  |
|-------------------------------------|----------------------------------|
| Mounting Hole Diameter D (Imperial) | 0.26 "                           |
| Mounting Hole Diameter D (Metric)   | 6.5 mm                           |
| Material                            | Polyamide 6.6 (PA66)             |
| Material Shortcut                   | PA66                             |
| Flammability                        | UL 94 V-2                        |
| Halogen Free                        | No                               |
| UV Resistant (Yes/No)               | No                               |
| Use Conditions                      | For Indoor and Outdoor Use       |
| Operating Temperature               | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33)        | Yes                              |
| ROHS Compliant                      | Yes                              |
| Package Quantity (Imperial)         | 50                               |
| Package Quantity (Metric)           | 50                               |
| Customs Number                      | 3926909988                       |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)