

Specification Sheet

Part Number: 151-02985



Can be easily assembled to convoluted tubing and reliably remain in position

Internal rib prevents movement or rattling

Multiple bracket configurations mount to a variety of surfaces

Releasable to allow for maintenance

Conduit Clamps, Size 19, Mounting Hole 10.6 mm, Offset 50.0 mm, PA66HIRHS, Black, 50/pkg

Article Number	151-02985
----------------	-----------

Type	CDC19B90OS50M10
------	-----------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The Convoluted Tubing Clamp provides a quick method for securing and routing convoluted tubing. The clamp has an internal rib that prevents movement of the tubing and rattling. Living hinge allows placement and positioning of tubing before locking in place. Convoluted tubing clamps are available in various tubing diameters. Choose from arrowhead, fir tree, bundling clip, bracket and dual clamp configurations.
---------------------	--

Short Description	Conduit Clamps, Size 19, Mounting Hole 10.6 mm, Offset 50.0 mm, PA66HIRHS, Black, 50/pkg
-------------------	--

Global Part Name	CDC19B90OS50M10-PA66HIRHS-BK
------------------	------------------------------

Length L (Imperial)	2.77
---------------------	------

Length L (Metric)	70.3
-------------------	------

Variant	Clamps
---------	--------

Width W (Imperial)	1.3
--------------------	-----

Width W (Metric)	32
------------------	----

Bundle Diameter Max (Imperial)	0.75
--------------------------------	------

Bundle Diameter Max (Metric)	19.0
------------------------------	------

Height H (Imperial)	3.53
---------------------	------

Height H (Metric)	89.6
-------------------	------

Inner Diameter D (Imperial)	1.08
-----------------------------	------

Inner Diameter D (Metric)	27.4
---------------------------	------

Diameter D (Imperial)	0.81
-----------------------	------

Diameter D (Metric)	20.6
---------------------	------

Nominal Diameter (Imperial)	0.75
-----------------------------	------

Nominal Diameter (Metric)	19.0
---------------------------	------

Mounting Hole Diameter D (Imperial)	0.42 "
Mounting Hole Diameter D (Metric)	10.6 mm
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)