

Specification Sheet

Part Number: 151-03101

Separates bundles to help prevent chafing and wear.

Single bundles can be mounted on top of the mount, or two bundles can be separated using the two side saddles; giving the mount versatility.



Low fire hazard materials comply with stringent NFPA 130 safety standards and improve opportunities to get product specified at the engineering stage of a project.

Low Profile Screw Mount, 1.8 x 0.98", 0.25" Hole, PA666V0, Black, 500/pkg

Article Number 151-03101

Type LPM25

Color Black (BK)

Quantity Per pack

Product Description Low-profile mounts secure bundles close to mounting surfaces, making them ideal for applications where bundle mounting space is limited. These are secured to the mounting surface with a 0.25" mechanical fastener and feature a counter bore for easy access with a socket. The mount accommodates cable ties up to 0.5" in width. Low fire hazard material is designed specifically for rail applications.

Short Description Low Profile Screw Mount, 1.8 x 0.98", 0.25" Hole, PA666V0, Black, 500/pkg

Global Part Name

LPM25-PA666V0-BK

Length L (Imperial) 1.8

Length L (Metric) 45.1

Fixation Method Screw Mounting and Rivet

Width W (Imperial) 0.98

Width W (Metric) 24.9

Cable Ties T50 - T250

Height H (Imperial) 0.66

Height H (Metric) 16.7

Mounting Hole Diameter D (Imperial) 0.25 "

Mounting Hole Diameter D (Metric) 6.7 mm

Mounting Hole Diameter D Max (Metric) 6.7

Material Polyamide 6.6/6, V0 (PA666V0)

Material Shortcut PA666V0

Flammability UL 94 V-0

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	Exova NFPA130: 2017 ASTM E 162 ASTM 1354 ASTM E 662
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)