

Specification Sheet

Part Number: 151-03253



Separates and secures bundles avoiding abrasion.

Designed to handle both convoluted tubing and bundles not covered in convoluted tubing.

Come in a variety of sizes and colors to be easily identified.

HDCM2 Clamp Bundle Separator, Two Hole, PA66HIRGF15, Black, 500/pkg

Article Number 151-03253

Type HDCM2A

Color Black (BK)

Quantity Per pack

Product Description HC Clamps separate multiple bundles and secure them to brackets or frame rails. Each mount has two pawls for easy pre-installation on a threaded fastener prior to securing with a mechanical fastener. HC Clamps have ribs that make them ideal for convoluted tubing, but they can also be used to separate separate bundles that aren't protected with convoluted tubing.

Short Description HDCM2 Clamp Bundle Separator, Two Hole, PA66HIRGF15, Black, 500/pkg

Length L (Imperial) 2.72

Length L (Metric) 69.1

Variant Separators

Width W (Imperial) 1.12

Width W (Metric) 28.48

Bundle Diameter Min (Imperial) 0.93

Bundle Diameter Min (Metric) 23.7

Bundle Diameter Max (Imperial) 0.93

Bundle Diameter Max (Metric) 23.7

Bundle Diameter 1st Loop Max (Imperial) 0.933

Bundle Diameter 1st Loop Max (Metric) 23.7

Bundle Diameter 2nd Loop Max (Imperial) 0.933

Bundle Diameter 2nd Loop Max (Metric) 23.7

Height H (Imperial) 1.34

Height H (Metric) 34

Mounting Hole Diameter D (Imperial)	0.32 "
Mounting Hole Diameter D (Metric)	8.2 mm
Material	Polyamide 6.6 glass fiber reinforced (PA66GF15%)
Material Shortcut	PA66GF15
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

