

Specification Sheet

Part Number: 151-03404



Edge clip applies easily to plastic and metal edges without the need for a mounting hole.

Tape bar provides a convenient surface for securing a bundle using a cable tie or tape.

Edge Clip and Tape Clip, EC14, Panel Thickness 0.04" - 0.12", 1.6" Long, PA66HIRHS, Black, 500/pkg

Article Number	151-03404
----------------	-----------

Type	EC14
------	------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's edge clips are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. These edge clips are molded to a tape bar, which can be secured to cables with cable ties or tape. The clip is easy to secure, and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.
---------------------	---

Short Description	Edge Clip and Tape Clip, EC14, Panel Thickness 0.04" - 0.12", 1.6" Long, PA66HIRHS, Black, 500/pkg
-------------------	--

Global Part Name	EC14-PA66HIRHS-BK
------------------	-------------------

Length L (Imperial)	1.6
Length L (Metric)	40.0
Fixation Method	Edge Clip
Width W (Imperial)	0.39
Width W (Metric)	10.0
Height H (Imperial)	0.49
Height H (Metric)	12.4
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No

Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)