

## Specification Sheet

Part Number: 151-03547

Smaller footprint for applications where space is constrained.

Attach using a bolt in an existing threaded hole, or bolt and nut for a non-threaded hole, for versatile mounting options.

Integrated metal bushing resists crushing when fastener is torqued down.



One-piece ratchet closure allows for fast and easy installation.

Clamp interior is designed to guide and center bundles to reduce pinching.

M6 Bolt Mount Ratchet Clamp, High Torque, 0.76 - 1.42" Bundle, PA66HIRHSUV, BK, 150/bg

Article Number 151-03547

Type CMRCCHM6

Color Black (BK)

Quantity Per pack

## Product Description

The Bolt Mount Ratchet Clamp offers versatility when managing conduit, wires, cables and hoses. It is specially designed for locations with space constraints or where offset mounting options are not ideal. Available with a compression limiter for crush resistance in high-torque applications, or in all-plastic for low- to medium-torque applications. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The adjustable clamp can be closed by hand to the desired diameter. The release feature allows easy and nondestructive removal or addition of cables simply by inserting a flat-head screwdriver. In this way, the clamp can be reused without removing it from the mounting surface.

## Short Description

M6 Bolt Mount Ratchet Clamp, High Torque, 0.76 - 1.42" Bundle, PA66HIRHSUV, BK, 150/bg

## Global Part Name

CMRCCHM6-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 250

Minimum Tensile Strength (Metric) 1112

Length L (Imperial) 4.93

Length L (Metric) 125.3

Fixation Method Screw Mount

Width W (Imperial) 1.38

Width W (Metric) 35.1

Bundle Diameter Min (Imperial) 0.76

Bundle Diameter Min (Metric) 19.3

Bundle Diameter Max (Imperial)	1.42
Bundle Diameter Max (Metric)	36.1
Height H (Imperial)	1.20
Height H (Metric)	30.4
Diameter D (Imperial)	0.28
Diameter D (Metric)	7.1
Bolt Size	0.236 "
Mounting Hole Diameter D (Imperial)	0.280 "
Mounting Hole Diameter D (Metric)	7.1 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 150

Package Quantity (Metric) 150

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)