

Specification Sheet

Part Number: 151-03650

No drilling or extra hardware required – just secure to steel surface.

Magnetic mounts are reliable even in debris, dirt, and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse and reposition capabilities allow for a flexible mounting solution.

Easily remove without residue.



Magnetic Pipe Mount, 1.02", Neodymium Magnet/POM/ST, 15lb Pull Force, 100/bag

Article Number	151-03650
Type	MAGCTM20P
Color	Black (BK)
Quantity Per	pack

Product Description	Magnetic cable tie mounts route bundles by securing to steel surfaces without the need for a mounting hole. Simply attach the wire bundle to the mount with a cable tie and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. The pipe mount has a unique shape to adhere perfectly to steel pipes. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts. Magnetic cable tie mounts can be paired with standard T18-T50 cable ties.
Short Description	Magnetic Pipe Mount, 1.02", Neodymium Magnet/POM/ST, 15lb Pull Force, 100/bag
Global Part Name	MAGCTM20P-NDFEB45M/POM/ST-BK
Length L (Imperial)	1.02
Length L (Metric)	26.0
Fixation Method	Magnet
Width W (Imperial)	0.27
Width W (Metric)	7.0
Height H (Imperial)	0.41
Height H (Metric)	10.5
Diameter D (Imperial)	0.55
Diameter D (Metric)	14.0

Cable Tie Width Max (Imperial)	0.23
Cable Tie Width Max (Metric)	5.84
Material	Steel (ST) Polyacetal (POM) Neodymium alloy 45M (NDFEB45M)
Material Shortcut	POM ST NDFEB45M
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	8505110070

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)