

Specification Sheet

Part Number: 151-03652

No drilling or extra hardware required – just position on steel surface.

Magnetic mounts are reliable even in debris, dirt and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse and reposition capabilities allow for a flexible mounting solution.



Saddle included to prevent kinking of cables.

Easily remove without leaving residue behind.

Article Number 151-03652

Type MAGBR90L-S

Color Metal (ML) Yellow (YE)

Quantity Per pack

Product Description

Magnetic bridle rings route cables by securing to steel surfaces without the need for a mounting hole. Simply attach cables within the bridle ring saddle and position the magnet onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. Magnetic bridle rings are ideal for supporting communication and data cables. The additional saddle helps prevent kinking of wires. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

Short Description

Magnetic Bridle Ring with Saddle, Large, 2" Dia Ring, Neodymium Magnet/PP/ST, 90lb Pull Force, 100/box

Global Part Name

MAGBR90L-S-NDFEB45M/ST/PP-ML/YE

Fixation Method

Magnet

Height H (Imperial)

3.90

Height H (Metric)

99.1

Diameter D (Imperial)

1.57

Diameter D (Metric)

40.0

Material

Neodymium alloy 45M (NDFEB45M) Polypropylene (PP) Steel (ST)

Material Shortcut

PP ST NDFEB45M

Halogen Free

Yes

UV Resistant (Yes/No) No

Plenum Rating AH-1

Operating Temperature -40°F to +176°F (-40°C to +80°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

UL Listed (US and Canada) Yes

Package Quantity (Imperial) 100

Package Quantity (Metric) 100

Customs Number 8505110070

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)