

Specification Sheet

Part Number: 151-03790

TPE layer protects cables and prevents rotation and axial slide, for a positive hold without crushing bundles.

Clamps are stackable to minimize space.

Anti-rotation feature prevents clamps from rotating while bolting down.

Releasable latch allows access to routings for serviceability.



Dual Bundle High Voltage Clamp, Anti-Rotation, 19 mm Bundle Dia, PA66GF15%/TPE, Black, 400/ctn

|                     |                                                                                                                                                                                                            |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 151-03790                                                                                                                                                                                                  |
| Type                | HDC19X2                                                                                                                                                                                                    |
| Color               | Black (BK)                                                                                                                                                                                                 |
| Quantity Per        | pack                                                                                                                                                                                                       |
| Product Description | This clamp system can protect HV cable wires in double cable routing applications and is secured using hardware. Clamp halves are sold individually; order two of these parts for every one clamp desired. |
| Short Description   | Dual Bundle High Voltage Clamp, Anti-Rotation, 19 mm Bundle Dia, PA66GF15%/TPE, Black, 400/ctn                                                                                                             |
| Global Part Name    | HDC19x2-PA66GF15/TPE-BK                                                                                                                                                                                    |

|                                         |               |
|-----------------------------------------|---------------|
| Length L (Imperial)                     | 3.24          |
| Length L (Metric)                       | 82.3          |
| Fixation Method                         | Stud Mount    |
| Width W (Imperial)                      | 1.02          |
| Width W (Metric)                        | 26.0          |
| Bundle Diameter Min (Imperial)          | 0.73          |
| Bundle Diameter Min (Metric)            | 18.5          |
| Bundle Diameter Max (Imperial)          | 0.77          |
| Bundle Diameter Max (Metric)            | 19.5          |
| Bundle Diameter 1st Loop Max (Imperial) | 0.77          |
| Bundle Diameter 1st Loop Max (Metric)   | 19.5          |
| Bundle Diameter 2nd Loop Max (Imperial) | 0.77          |
| Bundle Diameter 2nd Loop Max (Metric)   | 19.5          |
| Height H (Imperial)                     | 1.42          |
| Height H (Metric)                       | 36.0          |
| Mounting Hole Diameter D (Imperial)     | 0.31 x 0.05 " |

|                                   |                                                                                |
|-----------------------------------|--------------------------------------------------------------------------------|
| Mounting Hole Diameter D (Metric) | M8                                                                             |
| Mounting Hole Centers (Imperial)  | 1.73                                                                           |
| Material                          | Thermoplastic Elastomer (TPE) Polyamide 6.6 glass fiber reinforced (PA66GF15%) |
| Material Shortcut                 | PA66GF15 TPE                                                                   |
| Flammability                      | UL 94 HB                                                                       |
| Halogen Free                      | Yes                                                                            |
| UV Resistant (Yes/No)             | No                                                                             |
| Use Conditions                    | For Indoor Use Only                                                            |
| Operating Temperature             | -40°F to +257°F (-40°C to +125°C)                                              |
| Reach Compliant (Article 33)      | Yes                                                                            |
| ROHS Compliant                    | Yes                                                                            |
| Package Quantity (Imperial)       | 400                                                                            |
| Package Quantity (Metric)         | 400                                                                            |
| Customs Number                    | 3926909988                                                                     |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)