

Specification Sheet

Part Number: 151-03791

TPE layer protects cables and prevents rotation and axial slide, for a positive hold without crushing bundles.

Clamps are stackable to minimize space.

Anti-rotation feature prevents clamps from rotating while bolting down.

Releasable latch allows access to routings for serviceability.



Triple Bundle High Voltage Clamp, Anti-Rotation, 17 mm Bundle Dia, PA66GF15%/TPE, Black, 350/ctn

Article Number	151-03791
Type	HDC17X3
Color	Black (BK)
Quantity Per	pack
Product Description	This clamp system can protect HV cable wires in triple cable routing applications and is secured using hardware. Clamp halves are sold individually; order two of these parts for every one clamp desired.
Short Description	Triple Bundle High Voltage Clamp, Anti-Rotation, 17 mm Bundle Dia, PA66GF15%/TPE, Black, 350/ctn
Global Part Name	HDC17x3-PA66GF15/TPE-BK

Length L (Imperial)	4.97
Length L (Metric)	126.3
Fixation Method	Stud Mount
Width W (Imperial)	1.02
Width W (Metric)	26.0
Bundle Diameter Min (Imperial)	0.65
Bundle Diameter Min (Metric)	16.5
Bundle Diameter Max (Imperial)	0.69
Bundle Diameter Max (Metric)	17.5
Bundle Diameter 1st Loop Max (Imperial)	0.69
Bundle Diameter 1st Loop Max (Metric)	17.5
Bundle Diameter 2nd Loop Max (Imperial)	0.69
Bundle Diameter 2nd Loop Max (Metric)	17.5
Height H (Imperial)	1.42
Height H (Metric)	36.0
Mounting Hole Diameter D (Imperial)	0.31 x 0.05 "

Mounting Hole Diameter D (Metric)	M8
Mounting Hole Centers (Imperial)	1.73
Material	Thermoplastic Elastomer (TPE) Polyamide 6.6 glass fiber reinforced (PA66GF15%)
Material Shortcut	PA66GF15 TPE
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	350
Package Quantity (Metric)	350
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)