

Specification Sheet

Part Number: 151-03906



Bolt-down, one-piece design with 120-degree angle can bundle and secure two high-voltage cables inside convoluted tubing.

Integrated M6 Stud Mount acts as third hand for retention while attaching.

Compression limiter for high-torque bolted applications.

Releasable latch for serviceability.

Article Number	151-03906
Type	DHVC24M6A
Color	Black (BK)
Quantity Per	pack
Product Description	These clamps separate multiple bundles and secure them to any surface with a 6 mm stud or bolt. The one-piece hinged design snaps together to keep bundles such as tubing or battery cables separated. The robust design and durable materials also make it ideal for heavy duty applications.
Short Description	HV Dual Clamp with 120 degree M6 stud mount, 0.94" Bundle Dia, PA66HIRHSUV, Black, 200/ctn

Global Part Name	DHVC24M6A-PA66HIRHSUV-BK
------------------	--------------------------

Length L (Imperial)	4.04
---------------------	------

Length L (Metric)	102.5
-------------------	-------

Fixation Method	Stud Mount
-----------------	------------

Width W (Imperial)	1.20
--------------------	------

Width W (Metric)	30.5
------------------	------

Bundle Diameter Max (Imperial)	0.94
--------------------------------	------

Bundle Diameter Max (Metric)	24.0
------------------------------	------

Bundle Diameter 1st Loop Max (Imperial)	0.94
---	------

Bundle Diameter 1st Loop Max (Metric)	24.0
---------------------------------------	------

Bundle Diameter 2nd Loop Max (Imperial)	0.94
---	------

Bundle Diameter 2nd Loop Max (Metric)	24.0
---------------------------------------	------

Height H (Imperial)	1.26
---------------------	------

Height H (Metric)	31.5
-------------------	------

Mounting Hole Diameter D (Imperial)	0.24 "
-------------------------------------	--------

Mounting Hole Diameter D (Metric)	M6
-----------------------------------	----

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	200
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com