

## Specification Sheet

Part Number: 151-03989



Smaller footprint for applications where space is constrained.

Can be hand-twisted onto a threaded rod, allowing for quick installation, adjustment or removal.

Clamp interior is designed to guide and center bundles to reduce pinching.

1/4" Threaded Rod Mount Ratchet Clamp, 1.42 - 2.0" Bundle Dia, PA66HIRHSUV, Black, 25/bg

Article Number 151-03989

Type CMRCDR14

Color Black (BK)

Quantity Per pack

Product Description

The Threaded Rod Mount Ratchet Clamp offers versatility when managing conduit, wires, cables and hoses. Specially designed for locations with space constraints or where offset mounting options are not ideal. Easily twists onto existing threaded rods, eliminating the need for additional hardware. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The adjustable clamp can be closed by hand to the desired diameter. The release feature allows easy and nondestructive removal of cables simply by using a flat-head screwdriver. In this way, the clamp can be reused or serviced without removing it from the mounting surface.

Short Description	1/4" Threaded Rod Mount Ratchet Clamp, 1.42 - 2.0" Bundle Dia, PA66HIRHSUV, Black, 25/bg
Global Part Name	CMRCDTR14-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	250
Minimum Tensile Strength (Metric)	1112
Length L (Imperial)	5.89
Length L (Metric)	149.7
Fixation Method	1/4" Threaded Rod
Width W (Imperial)	1.38
Width W (Metric)	35.1
Bundle Diameter Min (Imperial)	1.42
Bundle Diameter Min (Metric)	36.1
Bundle Diameter Max (Imperial)	2
Bundle Diameter Max (Metric)	50.8
Height H (Imperial)	1.20
Height H (Metric)	30.4
Bolt Size	0.25 "

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)