

Specification Sheet

Part Number: 151-04005

Smaller footprint for applications where space is constrained.

Attach using a bolt in an existing threaded hole, or bolt and nut for a non-threaded hole, for versatile mounting options.



One-piece ratchet closure allows for fast and easy installation.

Clamp interior is designed to guide and center bundles to reduce pinching.

M6 Bolt Mount Ratchet Clamp, Low Torque, 0.50 - 0.77" Bundle, PA66HIRHSUV, BK, 25/bag

Article Number 151-04005

Type CMRCBLM6

Color Black (BK)

Quantity Per pack

Product Description

The Bolt Mount Ratchet Clamp offers versatility when managing conduit, wires, cables and hoses. It is specially designed for locations with space constraints or where offset mounting options are not ideal. Available with a compression limiter for crush resistance in high-torque applications, or in all-plastic for low- to medium-torque applications. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The adjustable clamp can be closed by hand to the desired diameter. The release feature allows easy and nondestructive removal or addition of cables simply by inserting a flat-head screwdriver. In this way, the clamp can be reused without removing it from the mounting surface.

Short Description

M6 Bolt Mount Ratchet Clamp, Low Torque, 0.50 - 0.77" Bundle, PA66HIRHSUV, BK, 25/bag

Global Part Name

CMRCBLM6-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 200

Minimum Tensile Strength (Metric) 889

Length L (Imperial) 3.39

Length L (Metric) 86.11

Fixation Method Screw Mount

Width W (Imperial) 1.38

Width W (Metric) 35.1

Bundle Diameter Min (Imperial) 0.5

Bundle Diameter Min (Metric) 12.7

| | |
|-------------------------------------|--|
| Bundle Diameter Max (Imperial) | 0.77 |
| Bundle Diameter Max (Metric) | 19.56 |
| Height H (Imperial) | 1.20 |
| Height H (Metric) | 30.48 |
| Diameter D (Imperial) | 0.25 |
| Diameter D (Metric) | 6.35 |
| Bolt Size | 0.236 " |
| Mounting Hole Diameter D (Imperial) | 0.248 " |
| Mounting Hole Diameter D (Metric) | 6.3 mm |
| Material | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut | PA66HIRHSUV |
| Flammability | UL 94 HB |
| Halogen Free | Yes |
| UV Resistant (Yes/No) | Yes |
| Use Conditions | For Indoor and Outdoor Use |

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

UL Listed (US) Yes

Package Quantity (Imperial) 25

Package Quantity (Metric) 25

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)