

Specification Sheet

Part Number: 151-04042



No drilling or extra hardware required – just position on steel surface.

Magnetic mounts are reliable even in debris, dirt and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse and reposition capabilities allow for a flexible mounting solution.

Easily remove without leaving residue behind.

Magnetic J-Hook 2" Dia. Hook, Top Mount, Neodymium Magnet/Steel, 90lb Pull Force, 100/Box

Article Number

151-04042

Type

MAGJH90TL

Color

Zinc-plated Metal (BV)

Quantity Per

pack

Product Description

Magnetic J-hooks route cables by securing to steel surfaces without the need for a mounting hole. Simply hang cables within the J-hook and position the magnet onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. Magnetic J-hooks are ideal for supporting communication and data cables. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

Short Description	Magnetic J-Hook 2" Dia. Hook, Top Mount, Neodymium Magnet/Steel, 90lb Pull Force, 100/Box
Global Part Name	MAGJH90TL-NDFEB45M/ST-ML
Fixation Method	Magnet
Width W (Imperial)	1.32
Width W (Metric)	33.53
Height H (Imperial)	4.82
Height H (Metric)	122.34
Depth D (Imperial)	2.0
Depth D (Metric)	50.80
Material	Steel (ST) Neodymium alloy 45M (NDFEB45M)
Material Shortcut	ST NDFEB45M
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only

Plenum Rating	AH-2
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	8505110070

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com