

Specification Sheet

Part Number: 151-04043



No drilling or extra hardware required – just position on steel surface.

Magnetic mounts are reliable even in debris, dirt and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse and reposition capabilities allow for a flexible mounting solution.

Easily remove without leaving residue behind.

Magnetic J-Hook 1-5/16" Dia Hook, Side Mount, Neodymium Magnet/Steel, 90lb Pull Force, 25/box

Article Number

151-04043

Type

MAGJH90SS

Color

Zinc-plated Metal (BV)

Quantity Per

pack

Product Description

Magnetic J-hooks route cables by securing to steel surfaces without the need for a mounting hole. Simply hang cables within the J-hook and position the magnet onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. Magnetic J-hooks are ideal for supporting communication and data cables. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

Short Description	Magnetic J-Hook 1-5/16" Dia Hook, Side Mount, Neodymium Magnet/Steel, 90lb Pull Force, 25/box
Global Part Name	MAGJH90SS-NDFEB45M/ST-ML
Fixation Method	Magnet
Width W (Imperial)	1.32
Width W (Metric)	33.53
Height H (Imperial)	3.88
Height H (Metric)	98.43
Depth D (Imperial)	1.55
Depth D (Metric)	39.37
Material	Steel (ST) Neodymium alloy 45M (NDFEB45M)
Material Shortcut	ST NDFEB45M
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only

Plenum Rating	AH-2
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	8505110070

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)