

Specification Sheet

Part Number: 151-04303

Made from our PA66HIRHS(REC100) post-industrial recycled material, this product offers exceptional performance in a wide range of industries and applications.

The ReSource family of products helps companies meet their sustainability goals.

Temporarily holds wires along routing path until ready to make permanent.

Built-in CutZone safety feature prevents damage to wires and cables.

Unique EZ Feed slot maintains clear space to insert cable ties.

Frame mount allows for simple quarter-turn mounting into 80/20, 40- or 15-Series aluminum frames.



Article Number	151-04303
Type	CTCM11CZF
Color	Black (BK)
Quantity Per	bag

Product Description	Part of our sustainable line of products, the ReSource product family features solutions made from post-industrial recycled material. It is impact resistant and heat stabilized for a range of operation environments and applications. This cradle mount with frame attachment can be twisted into industrial frames with a 0.7 x 0.31" frame mount and is ideal for routing wires in industrial applications where rework and adjustments are common. Mount features a 0.24" cradle opening for cable retention. The cradle arms can temporarily hold wires for simple adjustments and cable additions and protect against abrasion and cable damage. To permanently mount the bundle, the EZ Feed cable tie slot eliminates common obstructions for faster completion. During rework, the CutZone prevents wire damage when cutting off cable ties.
Short Description	Cradle Mount With Frame Attachment, 0.43" Cradle Area, 0.7 x 0.31" Frame Mount, PA66HIRHS(REC), Black, 100/Pkg
Global Part Name	CTCM11CZF-PA66HIRHS(REC)-BK
Length L (Imperial)	1.21
Length L (Metric)	30.9
Fixation Method	80/20 Frame
Width W (Imperial)	0.93
Width W (Metric)	23.73
Height H (Imperial)	1.27
Height H (Metric)	32.3
Cable Tie Width Max (Imperial)	0.51
Cable Tie Width Max (Metric)	13.0

Material	Polyamide 6.6 recycled, high impact modified, heat stabilized (PA66HIRHS(REC))
Material Shortcut	PA66HIRHS(REC)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com