

## Specification Sheet

Part Number: 151-04350



Compact size for mounting in tight spaces.

Modular connector clip design eliminates the need for investment in expensive tools for TPE products or upsetting of tubes and pipes.

Fine-pitch ratchet provides controlled grip for a range of pipe sizes with one part.

Fully enclosed clamp prevents slip, crush and fallout under vacuum.

Release latch with simple twist of screwdriver.

|                     |                                                                                                                                                                                                                                                                                                                                            |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 151-04350                                                                                                                                                                                                                                                                                                                                  |
| Type                | ROC18.5-22.5CLIP17                                                                                                                                                                                                                                                                                                                         |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                                                                 |
| Quantity Per        | carton                                                                                                                                                                                                                                                                                                                                     |
| Product Description | The Ratchet O-Clamp is designed for tight spaces, maintaining a low profile while providing an adjustable closure for a range of bundle sizes. HellermannTyton's connector clips provide a single method to mount connectors to various surfaces in a variety of applications. Clips can be paired with brackets for custom routing needs. |
| Short Description   | Ratchet O-Clamp, 0.73 - 0.88" Bundle Dia, 17 mm Connector Clip, PA66HIRHSUV, BK, 1000/ctn                                                                                                                                                                                                                                                  |

|                  |                                   |
|------------------|-----------------------------------|
| Global Part Name | ROC18.5-22.5CLIP17-PA66HIRHSUV-BK |
|------------------|-----------------------------------|

|                                     |     |
|-------------------------------------|-----|
| Minimum Tensile Strength (Imperial) | 100 |
|-------------------------------------|-----|

|                                   |     |
|-----------------------------------|-----|
| Minimum Tensile Strength (Metric) | 445 |
|-----------------------------------|-----|

|                     |      |
|---------------------|------|
| Length L (Imperial) | 2.29 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Length L (Metric) | 58.1 |
|-------------------|------|

|                 |                |
|-----------------|----------------|
| Fixation Method | Connector Clip |
|-----------------|----------------|

|                    |      |
|--------------------|------|
| Width W (Imperial) | 0.81 |
|--------------------|------|

|                  |      |
|------------------|------|
| Width W (Metric) | 20.5 |
|------------------|------|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Min (Imperial) | 0.73 |
|--------------------------------|------|

|                              |      |
|------------------------------|------|
| Bundle Diameter Min (Metric) | 18.5 |
|------------------------------|------|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Max (Imperial) | 0.88 |
|--------------------------------|------|

|                              |      |
|------------------------------|------|
| Bundle Diameter Max (Metric) | 22.5 |
|------------------------------|------|

|                     |      |
|---------------------|------|
| Height H (Imperial) | 1.89 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Height H (Metric) | 48.1 |
|-------------------|------|

|                              |                                                                          |
|------------------------------|--------------------------------------------------------------------------|
| Material                     | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut            | PA66HIRHSUV                                                              |
| Flammability                 | UL 94 HB                                                                 |
| Halogen Free                 | Yes                                                                      |
| UV Resistant (Yes/No)        | Yes                                                                      |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C)                                        |
| Reach Compliant (Article 33) | Yes                                                                      |
| ROHS Compliant               | Yes                                                                      |
| Package Quantity (Imperial)  | 1000                                                                     |
| Package Quantity (Metric)    | 1000                                                                     |
| Customs Number               | 3926909988                                                               |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com