

Specification Sheet

Part Number: 151-04353



Compact size for mounting in tight spaces.

Non-rotating fir tree provides easy insertion with high extraction resistance for 9x17 mm oval holes.

Fine-pitch ratchet provides controlled grip for a range of pipe sizes with one part.

Fully enclosed clamp prevents slip, crush and fallout under vacuum.

Release latch with simple twist of screwdriver.

Article Number	151-04353
Type	ROC18.5-22.5FT9X17
Color	Black (BK)
Quantity Per	carton
Product Description	The Ratchet O-Clamp is designed for tight spaces, maintaining a low profile while providing an adjustable closure for a range of bundle sizes. It is designed for fluid routing and high-voltage cable management. An integrated fir tree provides a secure grip into oval mounting holes with no additional hardware.
Short Description	Ratchet O-Clamp, 9x17mm Oval Fir Tree Mount, 0.73-0.88" Bundle Dia, PA66HIRHSUV, BK, 1000/ctn

Global Part Name	ROC18.5-22.5FT9X17-PA66HIRHSUV-BK
------------------	-----------------------------------

Minimum Tensile Strength (Imperial)	100
-------------------------------------	-----

Minimum Tensile Strength (Metric)	445
-----------------------------------	-----

Length L (Imperial)	2.29
---------------------	------

Length L (Metric)	58.1
-------------------	------

Fixation Method	Fir Tree
-----------------	----------

Width W (Imperial)	0.81
--------------------	------

Width W (Metric)	20.5
------------------	------

Bundle Diameter Min (Imperial)	0.73
--------------------------------	------

Bundle Diameter Min (Metric)	18.5
------------------------------	------

Bundle Diameter Max (Imperial)	0.88
--------------------------------	------

Bundle Diameter Max (Metric)	22.5
------------------------------	------

Height H (Imperial)	2.27
---------------------	------

Height H (Metric)	57.6
-------------------	------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.27
--------------------------------	------

Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.35 x 0.67 "
Mounting Hole Diameter D (Metric)	9.0 x 17.0 mm
Mounting Hole Diameter D Max (Metric)	17.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000

Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)