

Specification Sheet

Part Number: LKCRF19C2



Curved design for additional support of the bundle.

Simple to install with a screw or bolt.

Excellent security, particularly in areas of high vibration.

Low Profile Rivet Mount, 0.938" x .47", 0.25" Hole, Max Pan .134", T18-T50 Ties, 100/pkg

Article Number	151-27000
----------------	-----------

Type	LKCRF1
------	--------

Color	Natural (NA)
-------	--------------

Quantity Per	pack
--------------	------

Product Description	Low-profile rivet mount is designed for holding heavier cable bundles. Mounting bases can be used in many industries, they offer a very secure fixation and can be used with a wide variety of cable ties up to 4.8mm wide.
---------------------	---

Short Description	Low Profile Rivet Mount, 0.938" x .47", 0.25" Hole, Max Pan .134", T18-T50 Ties, 100/pkg
-------------------	--

Global Part Name	LKCRF1-PA66-NA
------------------	----------------

Length L (Imperial)	0.938
Length L (Metric)	24.0
Fixation Method	with Rivet (Mounts)
Width W (Imperial)	0.47
Width W (Metric)	12.0
Cable Ties	T18 - T50
Height H (Imperial)	0.157
Height H (Metric)	3.99
Cable Tie Width Max (Imperial)	0.18
Cable Tie Width Max (Metric)	4.8
Panel Thickness Max (Imperial)	0.134
Panel Thickness Max (Metric)	3.40
Mounting Hole Diameter D (Imperial)	0.25 "
Mounting Hole Diameter D (Metric)	6.4 mm
Mounting Hole Diameter D Max (Imperial)	0.255
Mounting Hole Diameter D Max (Metric)	6.4

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com