

Specification Sheet

Part Number: MB4SHA10H4



For use with HellermannTyton T18 - T50 cable ties to provide stability when securing bundles.

The rubber-based adhesive is an economical choice ideal for indoor applications, with a static load weight of 1.1 lb.

A predrilled hole extends mounting options and solutions.

Extended adhesive liner is easy to remove quickly.

Rubber Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, White, 500/pkg

|                     |                                                                                                                                                                                                                                                         |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 151-29206                                                                                                                                                                                                                                               |
| Type                | MB4SHA                                                                                                                                                                                                                                                  |
| Color               | White (WH)                                                                                                                                                                                                                                              |
| Quantity Per        | pack                                                                                                                                                                                                                                                    |
| Product Description | MB4SHA adhesive mounts are for use with HellermannTyton T18 - T50 Series cable ties to provide stability when securing bundles. The rubber adhesive-backed mounts can be used to secure a bundle and have a predrilled hole to extend mounting options. |
| Short Description   | Rubber Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, White, 500/pkg                                                                                                                                                         |

|                  |                |
|------------------|----------------|
| Global Part Name | MB4SHA-PA66-WH |
|------------------|----------------|

|                     |      |
|---------------------|------|
| Length L (Imperial) | 1.12 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Length L (Metric) | 28.3 |
|-------------------|------|

|                 |          |
|-----------------|----------|
| Fixation Method | Adhesive |
|-----------------|----------|

|                    |      |
|--------------------|------|
| Width W (Imperial) | 1.12 |
|--------------------|------|

|                  |      |
|------------------|------|
| Width W (Metric) | 28.3 |
|------------------|------|

|            |           |
|------------|-----------|
| Cable Ties | T18 - T50 |
|------------|-----------|

|                     |     |
|---------------------|-----|
| Height H (Imperial) | .23 |
|---------------------|-----|

|                   |     |
|-------------------|-----|
| Height H (Metric) | 5.8 |
|-------------------|-----|

|                                |      |
|--------------------------------|------|
| Cable Tie Width Max (Imperial) | 0.18 |
|--------------------------------|------|

|                              |     |
|------------------------------|-----|
| Cable Tie Width Max (Metric) | 4.6 |
|------------------------------|-----|

|                                     |        |
|-------------------------------------|--------|
| Mounting Hole Diameter D (Imperial) | 0.15 " |
|-------------------------------------|--------|

|                                   |        |
|-----------------------------------|--------|
| Mounting Hole Diameter D (Metric) | 3.9 mm |
|-----------------------------------|--------|

|          |                      |
|----------|----------------------|
| Material | Polyamide 6.6 (PA66) |
|----------|----------------------|

|                   |      |
|-------------------|------|
| Material Shortcut | PA66 |
|-------------------|------|

|                                |                                                 |
|--------------------------------|-------------------------------------------------|
| Adhesive                       | Synthetic rubber with base of polyethylene foam |
| Flammability                   | UL 94 V-2 (excluding adhesive)                  |
| UV Resistant (Yes/No)          | No                                              |
| Use Conditions                 | For Indoor Use Only                             |
| Adhesive Operating Temperature | 0°F to +150°F (-18 °C to +66 °C)                |
| Operating Temperature          | -40°F to +185°F (-40°C to +85°C)                |
| Reach Compliant (Article 33)   | Yes                                             |
| ROHS Compliant                 | Yes                                             |
| Package Quantity (Imperial)    | 500                                             |
| Package Quantity (Metric)      | 500                                             |
| Customs Number                 | 3926909988                                      |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com