

Specification Sheet

Part Number: S2HM250HIRHSH1

Separates bundles from wear and chafing, providing additional longevity.

Hexagonal retention feature (S2HM25) captures a bolt or nut requiring tool access from the back side only.

A socket counterbore allows securing with a socket wrench from the top side for use with a weld stud or bolt (S2CM25.)

Made from impact modified, heat stabilized, UV resistant material making it ideal for heavy duty applications.



Article Number	151-29403
----------------	-----------

Type	S2HM25
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's saddle mount can be installed between two bundles (such as wires, cables, hoses, tubing, conduit, etc.) to separate them and prevent chafing and wear. Fastened to a frame rail or mounting bracket, the H-profile on the saddle mount provides a tight circumferential loop on large and small bundles. Cable ties up to 1/2" wide are used to secure the bundles.
---------------------	---

Short Description	2-Way Saddle Mount, 3.5" Max Bundle Diameter, 0.25" Stud Diameter, PA66HIRHSUV, Black, 500/pkg
Global Part Name	S2HM25-PA66HIRHSUV-BK
Length L (Imperial)	1.80
Length L (Metric)	45.0
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	1.2
Width W (Metric)	30.0
Bundle Diameter Max (Imperial)	3.5
Bundle Diameter Max (Metric)	89.0
Cable Ties	T50 - T250
Height H (Imperial)	0.90
Height H (Metric)	23.0
Cable Tie Width Max (Imperial)	0.5
Cable Tie Width Max (Metric)	13.5
Mounting Hole Diameter D (Imperial)	0.24 " 0.25 " (HEXAGONAL)
Mounting Hole Diameter D (Metric)	6.0 mm 6.35 mm (hexagonal)

Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.25
Mounting Hole Diameter D Max (Metric)	6.0
Stud Diameter (Metric)	6.35 mm
Stud Diameter (Imperial)	0.25
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)