

## Specification Sheet

Part Number: 155-11601



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

Bundling Clip with Arrowhead, 2.17" Long, 0.06" - 0.12" Panel Thickness, PA66HIRHS, Black, 500/pkg

|                     |                                                                                                                                                                                           |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 155-11601                                                                                                                                                                                 |
| Type                | BCSFT6.5 16-3MD                                                                                                                                                                           |
| Color               | Black (BK)                                                                                                                                                                                |
| Quantity Per        | pack                                                                                                                                                                                      |
| Product Description | HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties. |
| Short Description   | Bundling Clip with Arrowhead, 2.17" Long, 0.06" - 0.12" Panel Thickness, PA66HIRHS, Black, 500/pkg                                                                                        |
| Global Part Name    | BCSFT6.5 16-3MD-PA66HIRHS-BK                                                                                                                                                              |

|                                         |               |
|-----------------------------------------|---------------|
| Length L (Imperial)                     | 2.17          |
| Length L (Metric)                       | 55.0          |
| Fixation Method                         | Arrowhead     |
| Width W (Imperial)                      | 0.32          |
| Width W (Metric)                        | 8.0           |
| Height H (Imperial)                     | 0.55          |
| Height H (Metric)                       | 14.0          |
| Panel Thickness Min (Imperial)          | 0.06          |
| Panel Thickness Max (Imperial)          | 0.12          |
| Panel Thickness Min (Metric)            | 1.5           |
| Panel Thickness Max (Metric)            | 3.0           |
| Mounting Hole Diameter D (Imperial)     | 0.25 - 0.26 " |
| Mounting Hole Diameter D (Metric)       | 6.3 - 6.7 mm  |
| Mounting Hole Diameter D Min (Imperial) | 0.25          |
| Mounting Hole Diameter D Max (Imperial) | 0.26          |
| Mounting Hole Diameter D Max (Metric)   | 6.7           |

|                              |                                                                  |
|------------------------------|------------------------------------------------------------------|
| Disc Diameter (Metric)       | 16.0                                                             |
| Disc Diameter (Imperial)     | 0.63                                                             |
| Material                     | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| Material Shortcut            | PA66HIRHS                                                        |
| Flammability                 | UL 94 HB                                                         |
| UV Resistant (Yes/No)        | No                                                               |
| Use Conditions               | For Indoor and Outdoor Use                                       |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C)                                |
| Reach Compliant (Article 33) | Yes                                                              |
| ROHS Compliant               | Yes                                                              |
| Package Quantity (Imperial)  | 500                                                              |
| Package Quantity (Metric)    | 500                                                              |
| Customs Number               | 3926909988                                                       |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)