

Specification Sheet

Part Number: 155-05400



Oval mount design pushes on easy by hand without the need for tools.

Design provides low insertion and high extraction force.

1-Piece 5.0mm Stud Mount Cable Tie with Oval Mounting Hole, 6.0" Long, 50lb Tensile Strength, PA66HS, Black, 500/pkg

Article Number	155-05400
Type	T50SOSSB5-HIGH-E
Color	Black (BK)
Quantity Per	pack
Product Description	The special oval shape provides for an approximate .20" (5.0 mm) lateral adjustment, allowing for any misalignment of the stud or incorrect positioning of the tie on the cables
Short Description	1-Piece 5.0mm Stud Mount Cable Tie with Oval Mounting Hole, 6.0" Long, 50lb Tensile Strength, PA66HS, Black, 500/pkg
Global Part Name	T50SOSSB5-HIGH-E-PA66HS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	170
Length L (Imperial)	6.0
Length L (Metric)	160
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.04
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Thickness T (Imperial)	0.05

Thickness T (Metric)	1.35
Stud Length Max (Imperial)	0.63
Stud Length Max (Metric)	16.0
Stud Length Min (Metric)	11.0
Stud Diameter (Metric)	5.0 mm
Stud Diamater (Imperial)	0.2
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500

Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)