

Specification Sheet

Part Number: 155-16301



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

Bundling Clip with Oval Fir Tree, 1.6" Long, 0.02 - 0.10" Panel Thickness, PA66HIRHS, Bk, 1000/pkg

Article Number	155-16301
Type	WICKELCLIP-VDS
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.
Short Description	Bundling Clip with Oval Fir Tree, 1.6" Long, 0.02 - 0.10" Panel Thickness, PA66HIRHS, Bk, 1000/pkg
Global Part Name	WICKELCLIP-VDS-PA66HIRHS-BK

Length L (Imperial)	1.6
Length L (Metric)	40.0
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.32
Width W (Metric)	8.0
Height H (Imperial)	0.42
Height H (Metric)	12.2
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.10
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	2.5
Mounting Hole Diameter D (Imperial)	0.25 - 0.39 " 0.25 - 0.35 "
Mounting Hole Diameter D (Metric)	6.3 x 9.0 mm 6.3 x 10.0 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.35
Mounting Hole Diameter D Max (Metric)	9.0

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com