

Specification Sheet

Part Number: 156-01667

Patented retention design on clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

Cable tie accommodates wide range of secondary bundle sizes.



MOC Clip, 16 mm, Assembled to T50SVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01667
----------------	-----------

Type	T50SVCMOC16M
------	--------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The MOC to Swivel Tie is a rotatable routing clip coupled to a cable tie that keeps two routings secured and separated. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness. The swivel coupler allows the two routings to rotate independently of each other.
---------------------	---

Short Description	MOC Clip, 16 mm, Assembled to T50SVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn
-------------------	---

Global Part Name	T50SVCMOC16M-PA66HIRHSUV-BK
------------------	-----------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	1.01
---------------------	------

Length L (Metric)	25.7
-------------------	------

Fixation Method	Omega Clip
-----------------	------------

Identification Plate Position	none
-------------------------------	------

Bundle Diameter Min (Imperial)	0.55
--------------------------------	------

Bundle Diameter Min (Metric)	14.0
------------------------------	------

Bundle Diameter Max (Imperial)	0.72
--------------------------------	------

Bundle Diameter Max (Metric)	18.3
------------------------------	------

Height H (Imperial)	1.48
---------------------	------

Height H (Metric)	37.5
-------------------	------

Depth D (Imperial)	0.47
--------------------	------

Depth D (Metric)	12.0
------------------	------

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)
[RoHS/WEEE Compliance](#)
[Disclaimer](#)
[Terms and Conditions](#)