

Specification Sheet

Part Number: 156-02383



Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.

Clip is reusable, making relocation or adjustments simple.

All-in-one bundling and mounting solution reduces costs.

LOC Locking Clamp, 10 - 14 mm, with T50SMVC Swivel Tie, PA66HIRHS/PA66HIRHSUV, Black, 1000/ctn

Article Number	156-02383
Type	T50SMVCLOC10-14
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.
Short Description	LOC Locking Clamp, 10 - 14 mm, with T50SMVC Swivel Tie, PA66HIRHS/PA66HIRHSUV, Black, 1000/ctn
Global Part Name	T50SMVCLOC10-14-PA66HS/PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.3
Length L (Metric)	210.0
Fixation Method	Omega Clip
Identification Plate Position	none
Width W (Imperial)	0.47
Width W (Metric)	12.0
Bundle Diameter Min (Imperial)	0.39
Bundle Diameter Min (Metric)	10.0
Bundle Diameter Max (Imperial)	0.55
Bundle Diameter Max (Metric)	14.0
Height H (Imperial)	0.93
Height H (Metric)	27.4
Depth D (Imperial)	0.47
Depth D (Metric)	12.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Polyamide 6.6 heat stabilized (PA66HS)
Foot Part Material	PA66HIRHSUV
Material Shortcut	PA66HS PA66HIRHSUV
Material Cable Tie	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)