

Specification Sheet

Part Number: 156-02794



- Anti-rotation pin eliminates movement of bundle when fastening bolt.
- Heavy duty mount with robust 120 lb tie delivers an ultra strong alternative to metal clamps.
- Assembly withstands vibrations and displacement forces.
- Metal bushing accommodates high tightening torque.

2-Piece Cable Tie with Screw Mount, Unassembled Set, 15"L, M6 Hole, 120lb, PA66HIRHSUV, Black, 500/ctn

Article Number	156-02794
Type	T120RHDM6TSSET
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton’s fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.
Short Description	2-Piece Cable Tie with Screw Mount, Unassembled Set, 15"L, M6 Hole, 120lb, PA66HIRHSUV, Black, 500/ctn

Global Part Name	T120RHDM6TSSET-PA66HIRHSUV-BK
------------------	-------------------------------

Minimum Tensile Strength (Imperial)	120
-------------------------------------	-----

Minimum Tensile Strength (Metric)	535
-----------------------------------	-----

Length L (Imperial)	15.0
---------------------	------

Length L (Metric)	390.0
-------------------	-------

Fixation Method	Screw Mount
-----------------	-------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.30
--------------------	------

Width W (Metric)	7.6
------------------	-----

Bundle Diameter Min (Imperial)	0.2
--------------------------------	-----

Bundle Diameter Min (Metric)	5.0
------------------------------	-----

Bundle Diameter Max (Imperial)	4.13
--------------------------------	------

Bundle Diameter Max (Metric)	105.0
------------------------------	-------

Thickness T (Imperial)	0.07
Thickness T (Metric)	1.8
Mounting Hole Diameter D (Imperial)	0.24
Mounting Hole Diameter D (Metric)	6.2 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)