


Specification Sheet

Part Number: 156-00013

Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.

2-piece design allows installer to slide clip around cable tie to obtain optimum orientation

Clip is reusable, making relocation or adjustments simple.



2-Piece Cable Tie with Pipe Clip, 6.0" Long, Attaches to Diameter 0.16 - 1.2", PA66HS, Black, 500/pkg

Article Number	156-00013
Type	T30ROC2A
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's 2-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.
Short Description	2-Piece Cable Tie with Pipe Clip, 6.0" Long, Attaches to Diameter 0.16 - 1.2", PA66HS, Black, 500/pkg
Global Part Name	T30ROC2A-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)	30
Minimum Tensile Strength (Metric)	135
Length L (Imperial)	5.8
Length L (Metric)	148.0
Fixation Method	Omega Clip
Identification Plate Position	none
Width W (Imperial)	0.14
Width W (Metric)	3.6
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4.0
Bundle Diameter Max (Imperial)	1.22
Bundle Diameter Max (Metric)	31.0
Height H (Imperial)	0.7
Height H (Metric)	16.8

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Foot Part Material	PA66HIRHS
Material Shortcut	PA66HIRHS PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com