

Specification Sheet

Part Number: 156-00155



Design provides quick and easy installation by hand without the need for tools

Multiple bundle diameters available for all different ranges of bundles

Clip allows 360 degrees of rotation to attach in any orientation

2-Piece Cable Tie with Pipe Clip, Diameter 0.26 - 0.31", 6.0" Long, PA66HS/PA66HIRHS, Black, 500/pkg

Article Number	156-00155
Type	T50SVC6.5
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's simple to use self-affixing tie allows the attaching of wires or hoses to an existing harness. This allows 360 degree rotation, and the ability to be oriented in any direction in relation to the main harness. This is ideally suited for any application in which the wire or hose can move in relation to the fixing point.
Short Description	2-Piece Cable Tie with Pipe Clip, Diameter 0.26 - 0.31", 6.0" Long, PA66HS/PA66HIRHS, Black, 500/pkg
Global Part Name	T50SVC6.5-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	222
Length L (Imperial)	6.1
Length L (Metric)	155.0
Fixation Method	Omega Clip
Identification Plate Position	none
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Foot Part Material	PA66HIRHS

Material Shortcut	PA66HIRHS PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com