

Specification Sheet

Part Number: 156-00264



Arrowhead design makes installation quick and easy by hand.

Ties "clicks" into place upon final installation signaling installer insertion is complete.

Design provides low insertion and high extraction force.

1-Piece Cable Tie with Arrowhead Mount with Seal, 6.3" Long, 50lb Tensile, PA66HS, Black, 3500/bg

Article Number	156-00264
Type	T50SOSSFT6.5E-MDL
Color	Black (BK)
Quantity Per	pack
Product Description	Arrowhead Push Ties with rubber seal secure fast and easy, while providing a special rubber seal to minimize water, dirt, or dust from getting through the mounting hole. The anchor adjusts for variations in panel thicknesses which insures a secure fixing at all times.
Short Description	1-Piece Cable Tie with Arrowhead Mount with Seal, 6.3" Long, 50lb Tensile, PA66HS, Black, 3500/bg
Global Part Name	T50SOSSFT6.5E-MDL-PA66HS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	6.3
Length L (Metric)	158.8
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.18
Bundle Diameter Max (Metric)	30.0
Thickness T (Imperial)	0.05

Thickness T (Metric)	1.3
Height H (Imperial)	0.67
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.07
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	1.8
Mounting Hole Diameter D (Imperial)	0.25 - 0.26 "
Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.7
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3500
Package Quantity (Metric)	3500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)