

Specification Sheet

Part Number: 156-00444



An all-in-one bundling and fastening solution that saves time and reduces costs.

Foam seal prevents ingress of moisture and debris and prevents vibration.

1-Piece Cable Tie with Arrowhead Mount with Seal, 8.5" Long, 50lb Tensile, PA66HIRHS, Natural, 500/bg

Article Number 156-00444

Type T50ROSAH6MDU

Color Natural (NA)

Quantity Per pack

Product Description The arrowhead design of these ties offers a low insertion force and a high extraction force. The foam rubber seal provides additional protection against moisture and debris. One-piece mounting ties offer a complete solution by simultaneously bundling and mounting cables, wires and hoses.

Short Description 1-Piece Cable Tie with Arrowhead Mount with Seal, 8.5" Long, 50lb Tensile, PA66HIRHS, Natural, 500/bg

Global Part Name T50ROSAH6MDU-PA66HIRHS-NA

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.5
Length L (Metric)	216.0
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.2
Width W (Metric)	5.0
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Panel Thickness Min (Imperial)	0.03

Panel Thickness Max (Imperial)	0.08
Panel Thickness Min (Metric)	0.8
Panel Thickness Max (Metric)	2.1
Mounting Hole Diameter D (Imperial)	0.24 - 0.26 "
Mounting Hole Diameter D (Metric)	6.2 - 6.6 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.6
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)