

## Specification Sheet

Part Number: 156-00878



Edge applications don't require additional fasteners or hole drilling.

Low push-on force reduces repetitive strain injuries.

Two-piece assembly allows mount to slide along strap, ensuring proper orientation.

Cable tie is outside serrated to reduce bundle chafing.

Outside Serrated Cable Tie with Edge Clip, 8.0" Long, EC24, 3 - 6 mm Panel, 50lb, PA66HS, Black, 500/pkg

Article Number

156-00878

Type

T50ROSEC24

Color

Black (BK)

Quantity Per

pack

Product Description

HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Short Description

Outside Serrated Cable Tie with Edge Clip, 8.0" Long, EC24, 3 - 6 mm Panel, 50lb, PA66HS, Black, 500/pkg

|                  |                                |
|------------------|--------------------------------|
| Global Part Name | T50ROSEC24-PA66HS/PA66HIRHS-BK |
|------------------|--------------------------------|

|                                     |    |
|-------------------------------------|----|
| Minimum Tensile Strength (Imperial) | 50 |
|-------------------------------------|----|

|                                   |     |
|-----------------------------------|-----|
| Minimum Tensile Strength (Metric) | 225 |
|-----------------------------------|-----|

|                     |     |
|---------------------|-----|
| Length L (Imperial) | 8.0 |
|---------------------|-----|

|                   |       |
|-------------------|-------|
| Length L (Metric) | 200.0 |
|-------------------|-------|

|                 |           |
|-----------------|-----------|
| Fixation Method | Edge Clip |
|-----------------|-----------|

|                               |      |
|-------------------------------|------|
| Identification Plate Position | none |
|-------------------------------|------|

|                    |    |
|--------------------|----|
| Releasable Closure | No |
|--------------------|----|

|         |                  |
|---------|------------------|
| Variant | Outside Serrated |
|---------|------------------|

|                    |      |
|--------------------|------|
| Width W (Imperial) | 0.18 |
|--------------------|------|

|                  |     |
|------------------|-----|
| Width W (Metric) | 4.6 |
|------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Min (Imperial) | 0.04 |
|--------------------------------|------|

|                              |     |
|------------------------------|-----|
| Bundle Diameter Min (Metric) | 1.0 |
|------------------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Max (Imperial) | 1.97 |
|--------------------------------|------|

|                              |      |
|------------------------------|------|
| Bundle Diameter Max (Metric) | 50.0 |
|------------------------------|------|

|                        |      |
|------------------------|------|
| Thickness T (Imperial) | 0.05 |
|------------------------|------|

|                                |                                                                                                         |
|--------------------------------|---------------------------------------------------------------------------------------------------------|
| Thickness T (Metric)           | 1.3                                                                                                     |
| Height H (Imperial)            | 0.05                                                                                                    |
| Height H (Metric)              | 1.3                                                                                                     |
| Panel Thickness Min (Imperial) | 0.12                                                                                                    |
| Panel Thickness Max (Imperial) | 0.24                                                                                                    |
| Panel Thickness Min (Metric)   | 3.0                                                                                                     |
| Panel Thickness Max (Metric)   | 6.0                                                                                                     |
| Material                       | Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| Foot Part Material             | PA66HIRHS                                                                                               |
| Material Shortcut              | PA66HS PA66HIRHS                                                                                        |
| Material Cable Tie             | Polyamide 6.6 heat stabilized (PA66HS)                                                                  |
| Flammability                   | UL 94 HB                                                                                                |
| UV Resistant (Yes/No)          | No                                                                                                      |
| Use Conditions                 | For Indoor and Outdoor Use                                                                              |
| Operating Temperature          | -40°F to +221°F (-40°C to +105°C)                                                                       |

|                              |            |
|------------------------------|------------|
| Reach Compliant (Article 33) | Yes        |
| ROHS Compliant               | Yes        |
| Package Quantity (Imperial)  | 500        |
| Package Quantity (Metric)    | 500        |
| Customs Number               | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)