

Specification Sheet

Part Number: 156-00953



Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

Fir tree provides low insertion effort yet demonstrates high extraction resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.

2-Piece Cable Tie with Fir Tree Mount, 5.8"L, Bundle Dia. 0.16 - 1.97" , PA66HIRHSUV/PA66HS, Black, 500/pkg

|                     |                                                                                                                                                                                                                                                                                                     |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 156-00953                                                                                                                                                                                                                                                                                           |
| Type                | T30RFT4                                                                                                                                                                                                                                                                                             |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                          |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                |
| Product Description | HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie. |
| Short Description   | 2-Piece Cable Tie with Fir Tree Mount, 5.8"L, Bundle Dia. 0.16 - 1.97" , PA66HIRHSUV/PA66HS, Black, 500/pkg                                                                                                                                                                                         |

|                  |                               |
|------------------|-------------------------------|
| Global Part Name | T30RFT4-PA66HIRHSUV/PA66HS-BK |
|------------------|-------------------------------|

|                                     |    |
|-------------------------------------|----|
| Minimum Tensile Strength (Imperial) | 30 |
|-------------------------------------|----|

|                                   |     |
|-----------------------------------|-----|
| Minimum Tensile Strength (Metric) | 135 |
|-----------------------------------|-----|

|                     |     |
|---------------------|-----|
| Length L (Imperial) | 6.0 |
|---------------------|-----|

|                   |       |
|-------------------|-------|
| Length L (Metric) | 148.0 |
|-------------------|-------|

|                 |                          |
|-----------------|--------------------------|
| Fixation Method | Fir tree for round holes |
|-----------------|--------------------------|

|                               |      |
|-------------------------------|------|
| Identification Plate Position | none |
|-------------------------------|------|

|             |              |
|-------------|--------------|
| Tie Closure | plastic pawl |
|-------------|--------------|

|         |                 |
|---------|-----------------|
| Variant | Inside Serrated |
|---------|-----------------|

|                    |      |
|--------------------|------|
| Width W (Imperial) | 0.14 |
|--------------------|------|

|                  |     |
|------------------|-----|
| Width W (Metric) | 3.6 |
|------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Min (Imperial) | 0.06 |
|--------------------------------|------|

|                              |     |
|------------------------------|-----|
| Bundle Diameter Min (Metric) | 1.5 |
|------------------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Max (Imperial) | 1.38 |
|--------------------------------|------|

|                              |      |
|------------------------------|------|
| Bundle Diameter Max (Metric) | 35.0 |
|------------------------------|------|

|                     |      |
|---------------------|------|
| Height H (Imperial) | 0.48 |
|---------------------|------|

|                                         |                                                                                                                 |
|-----------------------------------------|-----------------------------------------------------------------------------------------------------------------|
| Height H (Metric)                       | 11.8                                                                                                            |
| Panel Thickness Min (Imperial)          | 0.04                                                                                                            |
| Panel Thickness Max (Imperial)          | 0.12                                                                                                            |
| Panel Thickness Min (Metric)            | 1.0                                                                                                             |
| Panel Thickness Max (Metric)            | 3.0                                                                                                             |
| Mounting Hole Diameter D (Imperial)     | 0.13 - 0.16 "                                                                                                   |
| Mounting Hole Diameter D (Metric)       | 3.3 - 4.0 mm                                                                                                    |
| Mounting Hole Diameter D Min (Imperial) | 0.13                                                                                                            |
| Mounting Hole Diameter D Max (Imperial) | 0.16                                                                                                            |
| Mounting Hole Diameter D Max (Metric)   | 4.0                                                                                                             |
| Disc Diameter (Metric)                  | 13                                                                                                              |
| Material                                | Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Foot Part Material                      | PA66HIRHS                                                                                                       |
| Material Shortcut                       | PA66HS PA66HIRHSUV                                                                                              |
| UV Resistant (Yes/No)                   | Yes                                                                                                             |

|                              |                                                                     |
|------------------------------|---------------------------------------------------------------------|
| Use Conditions               | For Indoor and Outdoor Use                                          |
| Operating Temperature        | -40°F to +257°F (-40°C to +125°C) -40°F to +221°F (-40°C to +105°C) |
| Reach Compliant (Article 33) | Yes                                                                 |
| ROHS Compliant               | Yes                                                                 |
| Package Quantity (Imperial)  | 500                                                                 |
| Package Quantity (Metric)    | 500                                                                 |
| Customs Number               | 3926909988                                                          |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)